

Automatic Polishing Dropper HST-DYQ-6T



Product introduction

6 channels add different grinding media simultaneously at different speeds. It can be used in various grinding and polishing machines at home and abroad to automatically drop the polishing liquid to the grinding disc or polishing disc according to the speed required by different polishing materials to achieve the purpose of polishing.

Features

- Set each channel separately and work at the same time
- Connect with the polishing machine and drop the liquid according to the grinding and polishing parameters set by the grinding and polishing machine
- Two working modes: manual/online
- Each mode can be set independently: drip speed, drip time
- Automatic cleaning of dropper
- Larger or smaller drop speed, customizable

The online mode needs to be connected to a fully automatic grinding and polishing machine. When the grinding and polishing machine starts working, the dripper automatically starts running; after the grinding and polishing machine stops working, the dripper automatically stops working.

The main parameters

- HST-DYQ-T is a 6-channel dripper
- Drip speed: stepless speed regulation, about 6 drops/min -280 drops/min
- Maximum flow rate: 18 ml/min
- Maximum drip time: 9999 minutes and 59.9 seconds
- Power supply: AC 220V , 100W

HST GROUP Co., LTD.

NO. 4915, West Jingshi Road, Jinan 250012, PR CHINA.

Tel: +86-15866779269

www.hssdgroup.com E-mail: lisalee@hssdtest.com