

HST W4 Arc Spark Optical Emission Spectrometer



Picture just for reference

Summary:

HST-W4 Spectrometer is most suitable instrument for the determination of various elements in different matrices (Fe, Cu, Al, Ni, Co, Mg, Ti, Zn, Pb, Sn, Ag, etc). It is an economical and easy solution to quick analysis near the furnace, metal processing quality control and incoming material inspection, research laboratories and metal grade identification

This also gives the user a truly economical spectrometer that's both easy to use and easy to space saved. The optical system uses a CMOS detector with a spectral range covering all typical materials. It can accurately and reliably analyze from low-level elements to high-content elements. The compact structure design allows users to combine production and quality control more closely

Applications:

Steel plants where needs are at around 100 PPM levels or elements like C, Cr, S, P etc.

Rolling mills, foundries, workshops: Rapid analysis; test several 100s of samples daily

Alloy manufacturers: Any number of bases / matrices; highly stable and precise

Testing Laboratories: Commercial testing laboratories, Universities and colleges

Medium-sized industries: Extremely rugged and economical; low cost / analysis

Foundries which need a quick analysis near the furnace

Warehouse material identification

Base: Fe, Cu, Al, Ni, Co, Mg, Ti, Zn, Pb, Sn, Ag, etc

HST GROUP Co., LTD.

NO. 4915, West Jingshi Road, Jinan 250012, PR CHINA.

Tel: +86-159 1008 1986

www.hssdgroup.com - e-mail: admin@hssdtest.com